

THERMOLAST® K

General purpose, fogging

Typical applications

- Car mats
- · Function and design elements
- Handles (tools, toolboxes, skipoles)
- Seals
- Soft touch surface (thumb wheels, push buttons, switches)

Material advantages

- Adhesion to PP
- Easy coloring (compounds in natural colors)
- · Excellent mechanical properties
- · Excellent processing behavior
- Fulfills specifications for automotive interior
- Pleasant surface feel (Soft touch)
- UL 94 HB listed

Processing Method: Extrusion, Injection Molding

Product properties		
Compound name	TC6GPZ	
Series	GP/FG	
Color / RAL DESIGN	black	
Mechanical properties		
Hardness	59 ShoreA	DIN ISO 7619-1
Density	1.100 g/cm3	DIN EN ISO 1183-1
Tensile Strength ¹	8.0 MPa	DIN 53504/ISO 37
Elongation at Break ¹	750 %	DIN 53504/ISO 37
Tear Resistance	16.0 N/mm	ISO 34-1 Methode B (b)(Graves)
CS 72 h/23 °C	21 %	DIN ISO 815-1 Method A
CS 24 h/70 °C	34 %	DIN ISO 815-1 Method A
CS 24 h/100 °C	68 %	DIN ISO 815-1 Method A

¹ Deviating from ISO 37 standard test piece S2 is tested with a traverse speed of 200 mm/min.

Odour test acc. VW PV 3900 (VW 50180) @ 40 °C (2) level 3.0 / @ 80° C (3) level 3.

All values published in this data sheet are rounded average values.

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.




THERMOLAST® K

Compression Set

Compression Set (acc. DIN ISO 815)

For the compression set testing the following specimen is used: The specimen is a cylindrical disk shaped 6 mm thick and 13 mm in diameter.



The specimen is compressed by 25%. The compressed specimen is heated to the test temperature. DIN ISO 815 discribes two methods.

Method A: The specimen is allowed to recover immediately after its aging in the oven and then cooled down to room temperature. After 30 minutes the thickness of the specimen is measured and the compression set calculated.

Method B: The specimen is cooled down to room temperature after its aging in the oven and then allowed to recover.

Test results gained from method B are in general higher than from method A.

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.



THERMOLAST® K

	400,000,000,00	
Cylinder temperature	180 - 200 - 220 °C, max. 250 °C (360 - 390 - 430 °F, max. 480 °F)	
Hotrunner	Hot runner temperatures: 200 -250 °C (390 - 480 °F). The runner should be empty after a maximum (2 - 3 shots.	
Injection pressure	200 - 1000 bar (2900 - 14504 psi) (depending on the size and weight of the part).	
Injection rate	In general, the fill time should not be more than 1–2 seconds.	
Hold pressure	We recommend to derive the optimum hold pressure from determining the solidification point, starting with 40 $\%$ - 60 $\%$ of the required injection pressure.	
Back pressure	20 - 100 bar; if color batches are used, higher back pressure is necessary.	
Screw retraction	If an open nozzle is used processing with screw retraction is advisable.	
Mold temperature	25 - 40 °C (77 - 104 °F)	
Pre drying	Pre drying of the material is not necessary; if surface moisture forms as a result of changes in temperature, the material should be dried for 2 - 4 hours at 60 - 80 °C (140 - 175 °F).	
Needle valve	With materials < 50 Shore A the use of a needle valve is advisable.	
Screw geometry	Standard 3-zone polyolefine screw.	
Residence time	The residence time is to be set as short as possible with a maximum of 10 minutes.	
Cleaning recommendation	For cleaning and purging of the machine it is appropriate to use polypropylene or polyethylene. Machine must be PVC-free.	

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.



THERMOLAST® K

Processing Guideline Extrusion		
Cylinder temperature	160 - 180 - 200 °C, max. 250 °C (320 - 360 - 390 °F; max. 480 °F)	
Screw geometry	Standard three-zone screw (e.g. polyolefin screw). The screw must be able to provide sufficient shearing.	
L/D ratio	At least 25	
Compression ratio	At least 3.5 : 1	
Screens / breaker plate	A breaker plate and a screen pack are generally recommended in the extruder configuration in order to increase pressure.	
Die land	<= 3 mm (<= 0,12 in.)	
Extruder Head	Ca. 200 °C (390 °F)	
Die temperature	Ca. 200 - 230 °C (390 - 450 °F)	
Pre drying	Pre drying of the material is not necessary; if surface moisture forms as a result of changes in temperature, the material should be dried for 2 - 4 hours at 60 - 80 °C (140 - 175 °F).	
Calibration	Generally not necessary; support elements may be required when extruding THERMOLAST® compounds with high hardness or when coextruding with standard thermoplastics.	
Cleaning recommendation	For cleaning and purging of the machine it is appropriate to use polypropylene or polyethylene. Machine must be PVC-free.	

This datasheet is an extract of the KRAIBURG TPE program. Please contact KRAIBURG TPE to select the compound suitable for the requirements.